


Bulletin 900-CONV Front Display / Operations

Terminal Cover



Note: Cover the terminals to prevent electric shock.


Power Indicator

Lights (green) when line power is supplied.

Communications Setting Switch  
Used to set the communications conditions for connected devices.

Switch	Setting
1	
2	Baud Rate
3	
4	Data Length
5	
6	Parity
7	
8	Master Device
9	Slave Device
10	Echoback

Bulletin 900-CONVx  
without Terminal Cover



Communications Status Indicators

RD: Amber lights when receiving RS-485 communications.  
SD: Amber lights when sending RS-485 communications.

USB Port

(Use a commercially available USB cable)

M3.5 Terminal Screw

**Caution:** Make sure to use the Bulletin 900-CONV with the terminal cover mounted when using in machinery that must conform to EN/IEC standards.



Bulletin 900 — 900BuilderLite™ (Version 1.2\*) is FREE Personal Computer (PC) Configuration Software for Bulletin 900-TC8 and 900-TC16 Series B Temperature/Process Controllers.

- Provides a tabular fill-in-the-blanks on-line configuration and monitoring option to using the 900-TC8 or 900-TC16 controller's keypad and LED display
  - Simplifies controller configuration
  - Ability to save parameters to PC storage devices and retrieve as required
  - Configuration and monitoring can be done via direct or RS485 networked connection
  - Parameters can be saved as a .CSV format for use by Excel
- \* Version 1.2 must be used with the Series B 900-TC8 and 900-TC16. Version 1.1 must be used with Series A 900-TC8 and 900-TC16.

Table of Contents

Product Selection ..... 26

Product Selection

Description	Cat. No.
900BuilderLite Personal Computer Configuration Software for Bulletin 900-TC8 and 900-TC16 Temperature/Process Controllers with Enhanced Features	900-BLDLTSW1 *

\* Software is available FREE. To download software, go to the Bulletin 900 website found at: [www.ab.com/industrialcontrols/products/relays\\_timers\\_and\\_temp\\_controllers/single\\_loop\\_temp-heater\\_controllers/900tc.html](http://www.ab.com/industrialcontrols/products/relays_timers_and_temp_controllers/single_loop_temp-heater_controllers/900tc.html).

Go to "Get Software" (upper right of screen) and click on "900BuilderLite" and follow the download instructions.

Minimum Computer Hardware Requirements

- 300 MHz CPU
- 650 MB free disk space
- SVGA resolution monitor (XGA recommended)
- Microsoft Windows supported mouse
- Available serial 9-pin COM port (COM address 1 to 8) for connection to RS-232 option unit of 900-TC8 or RS-232 to RS-285 converter (Bulletin -CONVxx) for network connection to 31 Bulletin 900-TC8 and/or 900-TC15 controllers
- Available USB port for a direct connection to the 4-pin serial port of an enhanced Bulletin 900-TC8 or 900-TC16 controller using the 900-CPOEM1 to serial communication cable.

Computer Operating System Requirements

The following systems can be used with 900BuilderLite software.

- Microsoft Windows 2000/XP/Vista